



Artisan Technology Group is your source for quality new and certified-used/pre-owned equipment

- FAST SHIPPING AND DELIVERY
- TENS OF THOUSANDS OF IN-STOCK ITEMS
- EQUIPMENT DEMOS
- HUNDREDS OF MANUFACTURERS SUPPORTED
- LEASING/MONTHLY RENTALS
- ITAR CERTIFIED SECURE ASSET SOLUTIONS

SERVICE CENTER REPAIRS

Experienced engineers and technicians on staff at our full-service, in-house repair center

*InstraView*SM REMOTE INSPECTION

Remotely inspect equipment before purchasing with our interactive website at www.instraview.com ↗

WE BUY USED EQUIPMENT

Sell your excess, underutilized, and idle used equipment. We also offer credit for buy-backs and trade-ins. www.artisanng.com/WeBuyEquipment ↗

LOOKING FOR MORE INFORMATION?

Visit us on the web at www.artisanng.com ↗ for more information on price quotations, drivers, technical specifications, manuals, and documentation

Contact us: (888) 88-SOURCE | sales@artisanng.com | www.artisanng.com

FORENSICS CABINET

INSTALLATION, OPERATION, MAINTENANCE

INSTALLATION

TWO CABINETS ARE AVAILABLE, FLOOR AND BENCH-TOP MODELS. ON FLOOR UNITS, EFFORTS SHOULD BE MADE TO LEVEL AND PLUMB THE UNIT PRIOR TO MAKING EXHAUST CONNECTION.

- 1) BOTH UNITS REQUIRE CONNECTION TO A 120 VOLT, 20 AMP CIRCUIT AND TO AN EXTERNAL EXHAUST SYSTEM. SEE ROUGH-IN DETAILS AND WIRING DIAGRAM ON FOLLOWING PAGES.
- 2) CONNECT EXHAUST STACK OF CABINET TO AN EQUAL OR LARGER DIAMETER EXTERNALLY VENTED SYSTEM. EXHAUST SYSTEM MUST MEET CFM VALUES SPECIFIED ON FOLLOWING PAGES.

OPERATION

FOLLOW OPERATION LABEL AFFIXED TO FRONT PANEL OF UNIT. SEE COPY AT RIGHT.

DAMPER OPERATION

PULL DAMPER TO "OPEN"
PUSH DAMPER TO "CLOSE"

FUMING PROCEDURE

- 1 INSERT EVIDENCE INTO A CLEAN CHAMBER AND CLOSE THE DOOR AND DAMPER.
- 2 AFTER EVIDENCE IS PROPERLY EXPOSED, OPEN DAMPER AND EVACUATE THE CHAMBER WITH THE DOOR CLOSED FOR 5 MINUTES.
- 3 OPEN CHAMBER DOOR AND REMOVE EVIDENCE.
- 4 KEEP DAMPERS CLOSED ON CHAMBERS WHEN NOT IN USE.
- 5 CLEAN GLASS AND CHAMBER INTERIORS WEEKLY OR AS NEEDED.


THIS PANEL MAY BE REMOVED TO ACCESS VENT DAMPER FLENUM AND GUIDES FOR CLEANING OF INTERNAL COMPONENTS.

MAINTENANCE

- 1) PERIODIC CLEANING OF INTERIOR SURFACES IS RECOMMENDED TO MINIMIZE BUILD-UP OF DEVELOPING AGENTS. LAMINATE CLAD INTERIOR SURFACES AND GLASS DOOR PANELS MAY BE CLEANED WITH SOLVENTS AS RECOMMENDED BY DEVELOPING AGENT MFR. AVOID SOLVENT CONTACT ON WINDOW GLAZING AND VENT PORT GROMMETS.
- 2) RELAMP BY UNSCREWING INTERIOR GLASS GLOBE FROM LAMP HOUSING. DO NOT USE BULBS IN EXCESS OF 100 WATTS.
- 3) WIPE DOWN EXTERIOR SPILLS AS SOON AS POSSIBLE.
- 4) VERIFY PROPER AIRFLOW VOLUMES ANNUALLY. SEE FOLLOWING PAGES FOR SPECIFICATIONS.
- 5) REPLACE 'V'-SEAL DOOR GASKETS AS NECESSARY. SEAL IS AVAILABLE AT MOST HARDWARE STORES.
- 6) LUBRICATE DAMPERS AS REQUIRED FOR SMOOTH OPERATION.

PRODUCT DETAILS



BENCH-TOP UNIT 950P200



MINIMUM AIR FLOW - 13 CFM
 CONNECT TO 1.5" I.D. MINIMUM EXHAUST LINE

PRODUCT DETAILS


FULL HEIGHT UNIT 950P201



MINIMUM AIR FLOW - 32 CFM
 CONNECT TO 2.0" I.D. MINIMUM EXHAUST LINE

WIRING DIAGRAM


CONNECT TO 20 AMP CIRCUIT







Fisher Hamilton Inc.
1316 18th Street
Two Rivers, WI 54241
Tel: 920-793-1121
Fax: 920-793-3084

PL-641 Jan98 P/N 70776

950P200GY





950P201



Artisan Technology Group is your source for quality new and certified-used/pre-owned equipment

- FAST SHIPPING AND DELIVERY
- TENS OF THOUSANDS OF IN-STOCK ITEMS
- EQUIPMENT DEMOS
- HUNDREDS OF MANUFACTURERS SUPPORTED
- LEASING/MONTHLY RENTALS
- ITAR CERTIFIED SECURE ASSET SOLUTIONS

SERVICE CENTER REPAIRS

Experienced engineers and technicians on staff at our full-service, in-house repair center

*InstraView*SM REMOTE INSPECTION

Remotely inspect equipment before purchasing with our interactive website at www.instraview.com ↗

WE BUY USED EQUIPMENT

Sell your excess, underutilized, and idle used equipment. We also offer credit for buy-backs and trade-ins. www.artisanng.com/WeBuyEquipment ↗

LOOKING FOR MORE INFORMATION?

Visit us on the web at www.artisanng.com ↗ for more information on price quotations, drivers, technical specifications, manuals, and documentation

Contact us: (888) 88-SOURCE | sales@artisanng.com | www.artisanng.com