



Artisan Technology Group is your source for quality new and certified-used/pre-owned equipment

- FAST SHIPPING AND DELIVERY
- TENS OF THOUSANDS OF IN-STOCK ITEMS
- EQUIPMENT DEMOS
- HUNDREDS OF MANUFACTURERS SUPPORTED
- LEASING/MONTHLY RENTALS
- ITAR CERTIFIED SECURE ASSET SOLUTIONS

SERVICE CENTER REPAIRS

Experienced engineers and technicians on staff at our full-service, in-house repair center

*InstraView*SM REMOTE INSPECTION

Remotely inspect equipment before purchasing with our interactive website at www.instraview.com ↗

WE BUY USED EQUIPMENT

Sell your excess, underutilized, and idle used equipment. We also offer credit for buy-backs and trade-ins. www.artisanng.com/WeBuyEquipment ↗

LOOKING FOR MORE INFORMATION?

Visit us on the web at www.artisanng.com ↗ for more information on price quotations, drivers, technical specifications, manuals, and documentation

Contact us: (888) 88-SOURCE | sales@artisanng.com | www.artisanng.com

AJ™ Analog Joysticks

Features

- Two and three axis versions
- Compatible with 310M and 300, 1800 and 2000 Series controllers
- Pushbutton provides switch output



Analog Joysticks

The AJ-2 and AJ-3 Analog Joysticks provide an effective means of manually interfacing with positioning stages. The two-axis AJ-2 is ideally suited to the manual control of X-Y Tables, while the three axis AJ-3 allows a third axis to be controlled, via a spring centered rotary knob on the joystick shaft. Each model simply consists of two or three spring-centered potentiometers; when powered with a DC voltage, they output a voltage whose value is a function of the joystick angle. This value is then converted to velocity and direction by A/D converters and algorithms within the specific motor

controller. They are well suited for use with the 310M™ controller, and the 300™, 1800™, and 2000™ Series programmable controllers; refer to their Operator's Manuals for details. In general, a non-linear (typically cubic) transform is used to allow both very small and very large moves to be performed. When used with the 300 Series multi-axis controller, a joystick mounted pushbutton provides a switch output which the motion controller can interpret. Additional switches can be installed on the joystick base for special OEM applications.

SPECIFICATIONS

POTENTIOMETER RESISTANCE RANGE

1.5 Kohm - 2.0 Kohm ±10%

CONNECTOR

310M™ Controller: DB-25S

300™ Controller: DA-15P

1800™ & 2000™ Controllers: DE-9P

BASE DIMENSIONS

4-1/2" wide x 7-3/4" deep x 1-1/2" high

www.NEAT.COM

800.227.1066 • 603.893.0588





Artisan Technology Group is your source for quality new and certified-used/pre-owned equipment

- FAST SHIPPING AND DELIVERY
- TENS OF THOUSANDS OF IN-STOCK ITEMS
- EQUIPMENT DEMOS
- HUNDREDS OF MANUFACTURERS SUPPORTED
- LEASING/MONTHLY RENTALS
- ITAR CERTIFIED SECURE ASSET SOLUTIONS

SERVICE CENTER REPAIRS

Experienced engineers and technicians on staff at our full-service, in-house repair center

*InstraView*SM REMOTE INSPECTION

Remotely inspect equipment before purchasing with our interactive website at www.instraview.com ↗

WE BUY USED EQUIPMENT

Sell your excess, underutilized, and idle used equipment. We also offer credit for buy-backs and trade-ins. www.artisanng.com/WeBuyEquipment ↗

LOOKING FOR MORE INFORMATION?

Visit us on the web at www.artisanng.com ↗ for more information on price quotations, drivers, technical specifications, manuals, and documentation

Contact us: (888) 88-SOURCE | sales@artisanng.com | www.artisanng.com