



Artisan Technology Group is your source for quality new and certified-used/pre-owned equipment

- FAST SHIPPING AND DELIVERY
- TENS OF THOUSANDS OF IN-STOCK ITEMS
- EQUIPMENT DEMOS
- HUNDREDS OF MANUFACTURERS SUPPORTED
- LEASING/MONTHLY RENTALS
- ITAR CERTIFIED SECURE ASSET SOLUTIONS

SERVICE CENTER REPAIRS

Experienced engineers and technicians on staff at our full-service, in-house repair center

*InstraView*SM REMOTE INSPECTION

Remotely inspect equipment before purchasing with our interactive website at www.instraview.com ↗

WE BUY USED EQUIPMENT

Sell your excess, underutilized, and idle used equipment. We also offer credit for buy-backs and trade-ins. www.artisanng.com/WeBuyEquipment ↗

LOOKING FOR MORE INFORMATION?

Visit us on the web at www.artisanng.com ↗ for more information on price quotations, drivers, technical specifications, manuals, and documentation

Contact us: (888) 88-SOURCE | sales@artisanng.com | www.artisanng.com

Data Sheet

Analytical line / Calorimeters



C 2000 control version 2

The C 2000 basic IKA- calorimeter is a combustion calorimeter for determining gross calorific values of liquid and solid samples. A high level of automation with extremely simple handling characterizes this instrument. In addition to the isoperibolic measurement procedure (static jacket), a dynamic (reduced-time) working method is also available. To provide the calorimeter with cooling water, it needs to be connected to a thermostat f.e. IKA KV 600 (accessory) or a firmly installed water connection. The C 2000 control is equipped with a very convenient console to operate the unit.

- Automatic water handling system includes tempering, filling and emptying of calorimeter inner vessel
- Automatic oxygen filling of decomposition vessel
- Automatic decomposition vessel identification
- Automatic sample ignition
- Validation according to DIN 51900, ISO 1928, ASTM D240, ASTM D4809, ASTM D5865, ASTM D1989, ASTM D5468, ASTM E711
- Working methods:
isoperibol, measurement time: approx. 22 min
dynamic, measurement time: approx. 7 min
- Compact, integrated modular design for convenient operation
- Cooling water supply via thermostat f.e. IKA KV 600 (accessory) or firmly installed water connection (C 25 pressure regulating valve recommended)
- Interface connections for each of the following: scale, printer, monitor and sample rack C 5020
- User-friendly software C 5040 CalWin for controlling the calorimeter and administration of measuring data
- Up to eight measurement cells can be controlled by a single PC, using a multi-serial plug-in card PCI 8.2 (accessory)
- LIMS integration is possible
- Special halogen resistant vessel for quantitative decomposition of halogens and sulfur
- The decomposition vessel can be changed over to use combustible crucibles C 14 (accessory C5010.4 is needed)
- Consumables for calibrations and initial operation are included with delivery.
- A PC or notebook is required to operate the C 2000 control (not included with delivery)

Accessories: C 16 Parafilm, C 17 Paraffin, C 60 Conversion set for C 62, C 5010 Decomposition vessel, standard, C 5012 Decomposition vessel, halogen resistant, C 62 Decomposition vessel, "high pressure",

Technical Data	
Measuring range max. [J]	40000
Measuring mode adiabatic 22°C	no
Measuring mode isoperibol 22°C	no
Measuring mode dynamic 25°C	yes
Measuring mode isoperibol 25°C	yes
Measuring mode dynamic 30°C	yes
Measuring mode isoperibol 30°C	yes
Measuring mode double dry (ISO 1928)	no
Measuring time dynamic approx. [min]	7
Measuring time isoperibol approx. [min]	22
Reproducibility dynamic (1g benzoic acid NBS39i) [%RSD]	0.1
Reproducibility isoperibol (1g benzoic acid NBS39i) [%RSD]	0.05
Working temperature max. [°C]	30
Temperature measurement resolution [K]	0.0001
Cooling medium temperature min. [°C]	12
Cooling medium temperature max. [°C]	28
Cooling medium permissible operating pressure [bar]	1.5
Cooling medium	tap water
Type of cooling	flow
Flow rate min. [l/h]	0.3
Flow rate max. [l/h]	70
Oxygen operating pressure max. [bar]	40
Interface scale	RS232
Interface printer	Centronix
Interface PC	RS232
Interface test rack	yes
Interface ext. monitor	yes
Interface ext. keyboard	yes
Oxygen filling	yes
Degasification	no
Decomposition detection	yes
Decomposition vessel C 5010	no
Decomposition vessel C 5012	yes
Decomposition vessel C 7010	no
Decomposition vessel C 7012	no
Decomposition vessel C 62	no
Analysis according to DIN 51900 (1977/84)	yes



Artisan Technology Group is your source for quality new and certified-used/pre-owned equipment

- FAST SHIPPING AND DELIVERY
- TENS OF THOUSANDS OF IN-STOCK ITEMS
- EQUIPMENT DEMOS
- HUNDREDS OF MANUFACTURERS SUPPORTED
- LEASING/MONTHLY RENTALS
- ITAR CERTIFIED SECURE ASSET SOLUTIONS

SERVICE CENTER REPAIRS

Experienced engineers and technicians on staff at our full-service, in-house repair center

*InstraView*SM REMOTE INSPECTION

Remotely inspect equipment before purchasing with our interactive website at www.instraview.com ↗

WE BUY USED EQUIPMENT

Sell your excess, underutilized, and idle used equipment. We also offer credit for buy-backs and trade-ins. www.artisanng.com/WeBuyEquipment ↗

LOOKING FOR MORE INFORMATION?

Visit us on the web at www.artisanng.com ↗ for more information on price quotations, drivers, technical specifications, manuals, and documentation

Contact us: (888) 88-SOURCE | sales@artisanng.com | www.artisanng.com