



## Artisan Technology Group is your source for quality new and certified-used/pre-owned equipment

- FAST SHIPPING AND DELIVERY
- TENS OF THOUSANDS OF IN-STOCK ITEMS
- EQUIPMENT DEMOS
- HUNDREDS OF MANUFACTURERS SUPPORTED
- LEASING/MONTHLY RENTALS
- ITAR CERTIFIED SECURE ASSET SOLUTIONS

### SERVICE CENTER REPAIRS

Experienced engineers and technicians on staff at our full-service, in-house repair center

### *InstraView*<sup>SM</sup> REMOTE INSPECTION

Remotely inspect equipment before purchasing with our interactive website at [www.instraview.com](http://www.instraview.com) ↗

### WE BUY USED EQUIPMENT

Sell your excess, underutilized, and idle used equipment. We also offer credit for buy-backs and trade-ins. [www.artisanng.com/WeBuyEquipment](http://www.artisanng.com/WeBuyEquipment) ↗

### LOOKING FOR MORE INFORMATION?

Visit us on the web at [www.artisanng.com](http://www.artisanng.com) ↗ for more information on price quotations, drivers, technical specifications, manuals, and documentation

**Contact us:** (888) 88-SOURCE | [sales@artisanng.com](mailto:sales@artisanng.com) | [www.artisanng.com](http://www.artisanng.com)



## The New Enterprise PD2100 Refractometer

Temperature controlled, multi-detector platform for LS, RI, Viscometer detectors

### The New Enterprise PD2100 Refractometer

Advanced Detector for characterization of proteins, antibodies, viruses, polymers, and nanoparticles The New Enterprise PD2100 Differential Refractometer is the laser based differential refractometer which uses 680 nm. laser with temperature control chamber that operates from 4 to 50 °C providing the option for biological analysis at sub-ambient temperatures. The future of the system is designed to support additional detectors including Light scattering , UV, Viscometry detectors.

- 680 nm or 800 nm wavelength.  
Optional Wavelengths are also available.
- 8 uL Cell volume.
- 4 to 50 °C temperature control.
- Auto Purge.
- Calibrated for RI units.
- Windows Based Software Discovery32 Software for (dn/dc) determinations.
- Online Operation and Offline Operation
- Easy to read 6 Function Display
- USB interface



The "PD2100 Inside" configuration couples the PD2020 + within the optical chamber Enterprise PD2100 Differential Refractometer.

The "PD2100 Inside" configuration offers improved long term stability, accuracy and reproducibility and a means of virtually eliminating any band-broadening effects by placing only a few centimeters of tubing between the detectors.

### Enterprise PD2100 Differential Refractometer

Enterprise PD2100 Differential Refractometer is a new type of refractometer with optics specifically designed to operate with single wavelength laser light, the standard wavelength of light is 680 nm. other wavelengths are available upon request. The unit can be used for off-line measurements and is provided with software for easy analysis and can be linked to an auto sampler for fast easy through-put. When the detector is combined with GPC/SEC system it can used for online analysis, and when combined with our Discovery32 software UV/RI ratios can also be obtained to eliminate empirical errors. The system is designed with a thermoelectric heater cooling system using our unique convection oven system allowing other detectors to be combined inside the oven to provide full characterization of macromolecules.

Calibration:	The system is calibrated optically to provide accurate dn/dc calculations and can be validated on site with our internal standard calibration kit.
Electro Optics:	Uses a new style 3 dimensional positioning meter for the ultimate in reliability and linearity.
Sensitivity:	Comes for the unique electro optic design producing almost noise free signal levels for nanogram detection.
Cell Volume:	Low dispersion 8 micro liter cell with automatic purge.
Temperature:	The thermoelectric convention oven for multiple detector configurations.

This detector can be added to any GPC/HPLC system for normal RI detection and with its full temperature control capabilities it can be used with Proteins, Polymers and volatile solvents like Methylene Chloride (Dichloromethane)

**Taiwan and China Area:**

**Chia Yun Instrument Inc.**

佳允股份有限公司

TEL: +886-2-25419192 FAX: +886-2-25411553

E-mail: [chiayun@cyi-pmi.com](mailto:chiayun@cyi-pmi.com)

**Southeast Asia Area:**

**Porous Measurement Int'l Sdn. Bhd.**

Kuala Lumpur Office:

TEL: +60-3-42958324 H/P: +60-126954957

E-mail: [info@cyi-pmi.com](mailto:info@cyi-pmi.com)

Web site : [www.cyi-pmi.com](http://www.cyi-pmi.com)



## Artisan Technology Group is your source for quality new and certified-used/pre-owned equipment

- FAST SHIPPING AND DELIVERY
- TENS OF THOUSANDS OF IN-STOCK ITEMS
- EQUIPMENT DEMOS
- HUNDREDS OF MANUFACTURERS SUPPORTED
- LEASING/MONTHLY RENTALS
- ITAR CERTIFIED SECURE ASSET SOLUTIONS

### SERVICE CENTER REPAIRS

Experienced engineers and technicians on staff at our full-service, in-house repair center

### *InstraView*<sup>SM</sup> REMOTE INSPECTION

Remotely inspect equipment before purchasing with our interactive website at [www.instraview.com](http://www.instraview.com) ↗

### WE BUY USED EQUIPMENT

Sell your excess, underutilized, and idle used equipment. We also offer credit for buy-backs and trade-ins. [www.artisanng.com/WeBuyEquipment](http://www.artisanng.com/WeBuyEquipment) ↗

### LOOKING FOR MORE INFORMATION?

Visit us on the web at [www.artisanng.com](http://www.artisanng.com) ↗ for more information on price quotations, drivers, technical specifications, manuals, and documentation

**Contact us:** (888) 88-SOURCE | [sales@artisanng.com](mailto:sales@artisanng.com) | [www.artisanng.com](http://www.artisanng.com)