Spex 1682A Broad Band Radiation Source



In Stock

Used and in Excellent Condition

Open Web Page

https://www.artisantg.com/93968-1

All trademarks, brandnames, and brands appearing herein are the property of their respective owners.

- Critical and expedited services
- In stock / Ready-to-ship

- · We buy your excess, underutilized, and idle equipment
- · Full-service, independent repair center

ARTISAN'

Your definitive source for quality pre-owned equipment.

Artisan Technology Group

(217) 352-9330 | sales@artisantg.com | artisantg.com

Artisan Scientific Corporation dba Artisan Technology Group is not an affiliate, representative, or authorized distributor for any manufacturer listed herein.

Specialists in Spectroscopy

Optical Spectroscopy Division

Broad-Band Radiation Sources

Search

Products CCD Arrays

> **IR Arrays Detectors**

Monochromators

<u>Spectrographs</u>

Light Sources

Software

Accessories

Literature

Service

<u>Legacy</u>

Contact Us What's New? **OSD Home**

The LSH-T100 and LSH-T250 lamp housings are tungsten light sources of 100 and 250 watt, respectively. Forced air cooling is provided. The lamp housing includes a focusing mirror that collects radiation from the lamp and couples it to a location outside the housing. This design allows the housing to be mounted to a spectrometer with an accessory such as a



filter wheel or chopper mounted between the lamp and the spectrometer entrance slit.

LSH-T250 - Tungsten Source lamp housing, includes a 24 volt, 250 Watt tungsten halogen lamp. Requires a power supply such as the **LPS250**

LSH-T100 - Tungsten Source lamp housing, includes a 12 volt, 100 Watt tungsten halogen lamp. Requires a power supply such as the **LPS250**

1682AF - Tungsten-Halogen with deuterium or globar dual light source housing for 270M, 1681, 1680, 340E and 340S monochromators. Requires 1683L lamp and LPS250 power supply and/or 1684L lamp and 1684P power supply. If using with a 270M, LMK-270 mounting kit is also required.

1682AG - Tungsten-Halogen with deuterium or globar dual light source housing for 500M, 750M, 1000M, 1250M monochromators. Requires 1683L lamp and LPS250 power supply and/or 1684L lamp and 1684P power supply.

1682CF - Tungsten-Halogen light source with optical chopper for 270M, 1681, 1680, 340E and 340S monochromators. Requires 1683L lamp and LPS250 power supply.

1682CG - Tungsten-Halogen light source with optical chopper for 500M, 750M, 1000M, 1250M monochromators. Requires 1683L lamp and LPS250 power supply.

1682CG(CF)-2S - Tungsten-Halogen with deuterium or globar dual light source housing with optical chopper. Requires 1683L lamp and LPS250 power supply and/or 1684L lamp and 1684P power supply. If using with a TRIAX, LMK-270 mounting kit is also required. CG model for 500M, 750M, 1000M, 1250M monochromators. CF model for 270M, 1681, 1680, 340E and 340S monochromators.

For more information on these products we can be reached via e-mail or telephone:

Telephone (732) 494-8660 or 800-533-5946 Fax (732) 549-9309



www.jyinc.com

HORIBAGROUP

EMISSION • FLUORESCENCE • FORENSICS • GRATINGS & OEM INSTRUMENTS • OPTICAL SPECTR OSCOPY • RAMAN • THIN FILM

Home Page | Products | Contact Us | News & Events | Company Information | Jobs |

Artisan Technology Group is an independent supplier of quality pre-owned equipment

Gold-standard solutions

Extend the life of your critical industrial, commercial, and military systems with our superior service and support.

We buy equipment

Planning to upgrade your current equipment? Have surplus equipment taking up shelf space? We'll give it a new home.

Learn more!

Visit us at artisantg.com for more info on price quotes, drivers, technical specifications, manuals, and documentation.

Artisan Scientific Corporation dba Artisan Technology Group is not an affiliate, representative, or authorized distributor for any manufacturer listed herein.

We're here to make your life easier. How can we help you today? (217) 352-9330 | sales@artisantg.com | artisantg.com

