

Limited Availability
Used and in Excellent Condition

Open Web Page

https://www.artisantg.com/72698-1

the taken by

All trademarks, brandnames, and brands appearing herein are the property of their respective owners.

- Critical and expedited services
- In stock / Ready-to-ship

- We buy your excess, underutilized, and idle equipment
- · Full-service, independent repair center

ARTISAN'

Your **definitive** source for quality pre-owned equipment.

Artisan Technology Group

(217) 352-9330 | sales@artisantg.com | artisantg.com

Artisan Scientific Corporation dba Artisan Technology Group is not an affiliate, representative, or authorized distributor for any manufacturer listed herein.

# Performance features

MS5 and MZ6 stereomicroscopes

MS5 and MZ6 stereomicroscopes	
Design principle	Multiple-coated optical system with two parallel beam paths and one main objective (CMO)
Surface resistivity	
of antistatic material	<10 <sup>11</sup> ohms per square centimeter, discharge time <2 seconds from 1000V to 100V
Maximum numerical aperture	0.150 with 2.0× achromatic objective or 1.6× planapochromatic objective
	0.075 with 1.0× achromatic objective
Resolution	450 line-pairs / mm with 2.0× achromatic or 1.6× planapochromatic objective
	225 line-pairs / with 1.0× achromatic objective
Magnification changer	MS5: five-step, 0.63×, 1.0×, 1.6×, 2.5×, 4.0×
	MZ6: 6:1 zoom, 0.63× to 4.0×
Seven ratchet positions (MZ6)	at 0.8, 1, 1.25, 1.6, 2, 2.5, 3.2
Magnifications	$6.3 \times$ to $40 \times$ (with $1.0 \times$ objective and $10 \times$ eyepieces)
Total magnification	2× to 320×
Field diameter	0.8mm to 104.2mm
Working distances	81mm (1.0× plano), 97mm (0.63× planapo), 135mm (0.5× plano),
_	27mm-297mm (achromats)
Planachromatic and	$1.0 \times$ (plano, planapo), $0.5 \times$ (plano), $0.63 \times$ (planapo), $1.6 \times$ (planapo)
planapochromatic objectives	
Interchangeable achromatic	1.0×, 1.5×, 2.0×, 0.8×, 0.63×, 0.5×, 0.32×
objectives	
Wide-field eyepieces for	Distortion free, 10×/21B, 16×/14B, 25×/9.5B, 40×/6B
eyeglass wearers	
Dioptric correction	+5 to -5
Eyecups	Variable degree of eye contact
Binocular tubes	ErgoTube™ 10° to 50° with synchronized interpupillary adjustment
	Various ErgoModules™
Interpupillary distance	52 to 76mm
Stands, illuminators	
Focusing drive	Coarse, fine, manual and motorized, tiltable for OEM adaptations (bonders)
Length of column	300mm and 500mm, side-faced profile
Microscope carrier	Two basic heights, optics carrier rotatable through 360°,
	stereoscopic or vertical observation
Swing-arm stand	ESD version with 400/25m column, large stand with 550/50mm column,
	alternative with clamp for 20–50mm thick table tops
Universal stand	450/50mm or 800/50m column, 52cm × 34cm baseplate, magnetic carrier for stages
Transmitted-light stands	Bright field, bright and dark field, high-performance base
Stages	Various, including rotatable polarization stage
Incident lamps	Inclined, coaxial, vertical, fibre-optic light guides, fluorescence module
Accessories	
Photomicrographic systems	Leica MPS30 and MPS60, fully automatic, with data back
Video, filming,	Various configurations, Leica IC A integrated video module,
software for archiving and	Leica DC 100 and DC 200 digital imaging systems, image manager
for image processing	
Attachments for second observers	s For training and education
Drawing tube	For both left- and right-handed users
Double-iris diaphragm	For increasing the depth of field
Measuring graticules	For measuring lengths and for counting
Filter-slide housing	For two gelatine filters
Vertical and oblique observation	

## Artisan Technology Group is an independent supplier of quality pre-owned equipment

### **Gold-standard solutions**

Extend the life of your critical industrial, commercial, and military systems with our superior service and support.

### We buy equipment

Planning to upgrade your current equipment? Have surplus equipment taking up shelf space? We'll give it a new home.

#### Learn more!

Visit us at artisantg.com for more info on price quotes, drivers, technical specifications, manuals, and documentation.

Artisan Scientific Corporation dba Artisan Technology Group is not an affiliate, representative, or authorized distributor for any manufacturer listed herein.

We're here to make your life easier. How can we help you today? (217) 352-9330 | sales@artisantg.com | artisantg.com

