



Artisan Technology Group is your source for quality new and certified-used/pre-owned equipment

- FAST SHIPPING AND DELIVERY
- TENS OF THOUSANDS OF IN-STOCK ITEMS
- EQUIPMENT DEMOS
- HUNDREDS OF MANUFACTURERS SUPPORTED
- LEASING/MONTHLY RENTALS
- ITAR CERTIFIED SECURE ASSET SOLUTIONS

SERVICE CENTER REPAIRS

Experienced engineers and technicians on staff at our full-service, in-house repair center

*InstraView*SM REMOTE INSPECTION

Remotely inspect equipment before purchasing with our interactive website at www.instraview.com ↗

WE BUY USED EQUIPMENT

Sell your excess, underutilized, and idle used equipment. We also offer credit for buy-backs and trade-ins. www.artisanng.com/WeBuyEquipment ↗

LOOKING FOR MORE INFORMATION?

Visit us on the web at www.artisanng.com ↗ for more information on price quotations, drivers, technical specifications, manuals, and documentation

Contact us: (888) 88-SOURCE | sales@artisanng.com | www.artisanng.com

Canada
English

Cart: 0 Items

Log In/Register | My Bio-Rad | Contact Us | Help | [Corporate](#)[Products](#) [Solutions](#) [Promotions](#) [News & Events](#) [Support](#)

Life Science Research ▾

[Home](#) > [Life Science Research](#) > [Products](#) > [Chromatography](#) > [Instrument Systems, Components & Accessories](#) > [Low-Pressure Chromatography Components](#) > Model EG-1 Econo Gradient Monitor

Model EG-1 Econo Gradient Monitor



Overview

Econo Gradient
PumpEG-1 Econo
Gradient Pump

Find Products & Information

Entire site

Search

Get Help

Call us at 1-800-268-0213

Email a [quick question](#)Find [local contacts](#)Get [product support](#)Request a [quote](#)

Related Products

[BioFrac Fraction Collector](#)[Econo Gradient Pump Kits](#)[BioLogic DuoFlow 10 System](#)[Description](#) [Specifications](#) [Ordering](#) [Accessories](#)

Operating mode	Conductivity, in Siemens
Operating temperature	4–40°C
Sensitivity ranges (full scale)	0–10 μ S, 0–100 μ S, 0–10 mS,
Output signal	0–1 V
Power requirements	90–264 V, 50–60 Hz (depending upon power adaptor used)
Power consumption	20 W maximum
Noise	Short term: <0.1 μ S Long term: <0.5 μ S
Linearity	\pm 0.5% full scale
Accuracy	\pm 2% full scale
Drift	<0.5 μ S/hr°C
Dimensions	
Control unit	15.60 x 22.86 x 8.89 cm (W x L x H)
Flow Cell	3.1 cm diameter by 3.8 cm length
Weight	Control unit: 600g
Case material	Chemical and fire resistant polypropylene
Regulatory	CSA: C22.2 No. 151-M1986
Compliance	TUV: EN61010–1:1993 CE: EN50082–2:1995 EN55011: 1991 Class A
Flow Cell	
Type	Flow through, externally mounted
Temperature compensation	0–60 μ C
Internal volume	8 μ l, swept volume
Cell constant	Approximately 40°
Maximum operating pressure	60 psi, 4 bar, or 0.41 mPa
Cable length	1.22 M
Wetted parts	Titanium, Kel-F and Tefzel
Fittings	Removable luer (will also accept 1/4"–28 flat bottom fittings)

Promotions

Get a great deal on our newest cell counting solution: up to 20% off!

Don't miss out on a great cuvette deal!

Buy 2, Get 1 FREE: Any SsoFast™ EvaGreen® Supermix.

[See all »](#)

News & Events

News

[New Bio-Rad Video Shows Best Practices for Simplifying Gene Expression Studies](#)[Bio-Rad Introduces Methods for the Rapid Purification of Tag-Free Recombinant Proteins from Eukaryotic and Bacterial Systems](#)[Bio-Rad Introduces REDFIN 2-D Analysis Service to Simplify 2-D Gel Analysis](#)[Bio-Rad's New SsoFast™ Probes Supermix Accelerates Gene Expression Analysis](#)[Collaboration Between Bio-Rad and Layerlab Enables High Throughput Kinetic Analysis of Any Transmembrane Protein](#)[See all »](#)

Find a Certificate of Analysis

Catalog Number

Lot/Control Number

[» Need Help?](#)

Submit

[Home](#) | [Life Science Research](#) | [Clinical Diagnostics](#) | [Spectroscopy](#) | [Process Separations](#) | [Food/Animal/Environment Testing](#) | [Life Science Education](#)
[Help](#) | [Contact Us](#) | [Careers](#) | [Trademarks](#) | [Site Terms](#) | [Privacy](#)

Copyright © 2010 Bio-Rad Laboratories, Inc. All rights reserved.



Artisan Technology Group is your source for quality new and certified-used/pre-owned equipment

- FAST SHIPPING AND DELIVERY
- TENS OF THOUSANDS OF IN-STOCK ITEMS
- EQUIPMENT DEMOS
- HUNDREDS OF MANUFACTURERS SUPPORTED
- LEASING/MONTHLY RENTALS
- ITAR CERTIFIED SECURE ASSET SOLUTIONS

SERVICE CENTER REPAIRS

Experienced engineers and technicians on staff at our full-service, in-house repair center

*InstraView*SM REMOTE INSPECTION

Remotely inspect equipment before purchasing with our interactive website at www.instraview.com ↗

WE BUY USED EQUIPMENT

Sell your excess, underutilized, and idle used equipment. We also offer credit for buy-backs and trade-ins. www.artisanng.com/WeBuyEquipment ↗

LOOKING FOR MORE INFORMATION?

Visit us on the web at www.artisanng.com ↗ for more information on price quotations, drivers, technical specifications, manuals, and documentation

Contact us: (888) 88-SOURCE | sales@artisanng.com | www.artisanng.com