



## Artisan Technology Group is your source for quality new and certified-used/pre-owned equipment

- FAST SHIPPING AND DELIVERY
- TENS OF THOUSANDS OF IN-STOCK ITEMS
- EQUIPMENT DEMOS
- HUNDREDS OF MANUFACTURERS SUPPORTED
- LEASING/MONTHLY RENTALS
- ITAR CERTIFIED SECURE ASSET SOLUTIONS

### SERVICE CENTER REPAIRS

Experienced engineers and technicians on staff at our full-service, in-house repair center

### *InstraView*<sup>SM</sup> REMOTE INSPECTION

Remotely inspect equipment before purchasing with our interactive website at [www.instraview.com](http://www.instraview.com) ↗

### WE BUY USED EQUIPMENT

Sell your excess, underutilized, and idle used equipment. We also offer credit for buy-backs and trade-ins. [www.artisanng.com/WeBuyEquipment](http://www.artisanng.com/WeBuyEquipment) ↗

### LOOKING FOR MORE INFORMATION?

Visit us on the web at [www.artisanng.com](http://www.artisanng.com) ↗ for more information on price quotations, drivers, technical specifications, manuals, and documentation

**Contact us:** (888) 88-SOURCE | [sales@artisanng.com](mailto:sales@artisanng.com) | [www.artisanng.com](http://www.artisanng.com)

## Data Sheet

Laboratory reactors / Laboratory Reactors



### LR 2000 V (vacuum)

Stand LR 2000.70 for vacuum variant LR 2000 V. Please contact IKA® for a detailed quotation for the complete system.

The system LR 2000 V is a modularly expandable laboratory reactor, designed and planned for reproducing and optimizing chemical reaction processes as well as mixing, dispersing and homogenization processes at laboratory scales.

Some examples for these processes are:

- Manufacturing of cremes, lotions, emulsions, and liposome preparations in the pharmaceutical and cosmetic sector
- Mixing of solids such as calcium carbonate, talc, titanium oxide, etc. into liquid polymers
- Mixing of additives and solid polymer compounds into mineral oils
- Grinding and disintegrating of solids and fibers in liquids and polymers

The laboratory reactor LR 2000 V (vacuum) is especially designed for the use in the pharmaceutical and cosmetic sector.

The system can be adapted individually to a wide range of different applications and specific requirements. IKA® laboratory devices, e.g. temperature and pH measuring instruments, laboratory stirrers and dispersing instruments, pumps and thermostats can be combined and controlled via PC using labworldsoft®. The torque measuring instruments VK 600 control VISCOCLICK® or VM 600 basic allow for evaluation of rheological properties.

The IKA® laboratory reactor features among others are:

- Modularly expandable to accommodate interchangeable instruments for various applications (3 x NS 29 and 2 x NS 14 ground joints)
- Single- and double-walled jacketed 2 liter vessels available made of borosilicate glass or stainless steel, with or without bottom discharge valve
- Sealing materials (FFPM) resist solvents and temperatures for applications up to 230 °C

Technical Data	
Usable volume min. [ml]	500
Usable volume max. [ml]	2000
Working temperature min. [°C]	room temp.
Working temperature max. [°C]	230
Pressure max. [bar]	1
Attainable vacuum [mbar]	25
Viscosity max. [mPas]	150000
Speed range [1/min]	8 - 290
Telescope stand stroke [mm]	260
Material in contact with medium	borosilicate glass, FFPM, PTFE, steel 1.4571
Reactor vessel openings (units/standard)	3/NS 29/32 2/NS 14/23"
Dimensions (W x H x D) [mm]	500 x 1350 x 500
Weight [kg]	30
Permissible ambient temperature [°C]	5 - 40
Permissible relative moisture [%]	80
Protection class according to DIN EN 60529	IP 42
RS 232 interface	yes
Analog output	yes
Voltage [V]	230
Frequency [Hz]	50/60
Power input [W]	130
<b>Ident. No.</b>	<b>2509000</b>



## Artisan Technology Group is your source for quality new and certified-used/pre-owned equipment

- FAST SHIPPING AND DELIVERY
- TENS OF THOUSANDS OF IN-STOCK ITEMS
- EQUIPMENT DEMOS
- HUNDREDS OF MANUFACTURERS SUPPORTED
- LEASING/MONTHLY RENTALS
- ITAR CERTIFIED SECURE ASSET SOLUTIONS

### SERVICE CENTER REPAIRS

Experienced engineers and technicians on staff at our full-service, in-house repair center

### *InstraView*<sup>SM</sup> REMOTE INSPECTION

Remotely inspect equipment before purchasing with our interactive website at [www.instraview.com](http://www.instraview.com) ↗

### WE BUY USED EQUIPMENT

Sell your excess, underutilized, and idle used equipment. We also offer credit for buy-backs and trade-ins. [www.artisanng.com/WeBuyEquipment](http://www.artisanng.com/WeBuyEquipment) ↗

### LOOKING FOR MORE INFORMATION?

Visit us on the web at [www.artisanng.com](http://www.artisanng.com) ↗ for more information on price quotations, drivers, technical specifications, manuals, and documentation

**Contact us:** (888) 88-SOURCE | [sales@artisanng.com](mailto:sales@artisanng.com) | [www.artisanng.com](http://www.artisanng.com)