



Artisan Scientific

QUALITY INSTRUMENTATION ... GUARANTEED

Looking for more information?

Visit us on the web at <http://www.artisan-scientific.com> for more information:

- Price Quotations
- Drivers
- Technical Specifications, Manuals and Documentation

Artisan Scientific is Your Source for Quality New and Certified-Used/Pre-owned Equipment

- Tens of Thousands of In-Stock Items
- Hundreds of Manufacturers Supported
- Fast Shipping and Delivery
- Leasing / Monthly Rentals
- Equipment Demos
- Consignment

Service Center Repairs

Experienced Engineers and Technicians on staff in our State-of-the-art Full-Service In-House Service Center Facility

InstraView™ Remote Inspection

Remotely inspect equipment before purchasing with our Innovative InstraView™ website at <http://www.instraview.com>

We buy used equipment! We also offer credit for Buy-Backs and Trade-Ins

Sell your excess, underutilized, and idle used equipment. Contact one of our Customer Service Representatives today!

Talk to a live person: 888-88-SOURCE (888-887-6872) | Contact us by email: sales@artisan-scientific.com | Visit our website: <http://www.artisan-scientific.com>

Data Sheet

Distilling / Rotary Evaporators



RV 05 basic 2-B

- Newly designed! Consisting of heating bath HB 4 basic, set of glassware RV 06.2 with vertical condenser (space-saving), drive RV 05 basic, telescopic stand RV 05.3 and boss head clamp R 271.
- Easy and jolt-free raising and lowering of the rotary evaporator
 - Telescopic stand tiltable to the side
 - Rodaviss screw joint allows bonded ground joints to be released easily, removable screw connections facilitate cleaning of glass components
 - New condenser geometry with 1,200 cm² cooling surface, higher yield and cooler condensate constitute a contribution to environmental protection
 - No chimney effect, no foaming

Accessories: RV 06.4 Evaporating flask, NS 29, VC 2 IKAVAC® Vacuum controller, RV 05.3 Telescopic stand, RV 06.13 Seal, RV 06.11 Vapor tube, RV 06.15 Seal, VC 2.4 Pump control, RV 06.5 Evaporating flask, NS 29, RV 06.6 Evaporating flask, NS 29, RV 06.7 Receiving flask, KS 35, RV 06.1 Set of glassware, RV 06.2 Set of glassware, VC 1.1 Water jet pump, VC 1.3 Magnetic solenoid valve, RV 05 basic, HB 4 basic Heating bath

Technical Data	
Type of cooling	vertical
Cooling surface [cm ²]	1200
Evaporator capacity [ml/h]	1000
Motor principle	asynchronous
Motor rating input [W]	133
Motor rating output [W]	65
Speed range [1/min]	46 - 260
Lift	manual
Stroke [mm]	190
Heating temperature range [°C]	room temp. - 225
Heat output [W]	1000
Heat control accuracy [±K]	5
Bath volume max. [l]	4
Vacuum controller integrated	no
Dimensions (W x H x D) [mm]	580 x 1000 x 480
Weight [kg]	12
Permissible ambient temperature [°C]	5 - 40
Permissible relative moisture [%]	80
Protection class according to DIN EN 60529	IP 20
RS 232 interface	no
Analog output	no
Voltage [V]	220 - 240 / 100 - 120 / 100 - 115
Frequency [Hz]	50/60
Power input [W]	1133
Ident. No.	8018000



Artisan Scientific

QUALITY INSTRUMENTATION ... GUARANTEED

Looking for more information?

Visit us on the web at <http://www.artisan-scientific.com> for more information:

- Price Quotations
- Drivers
- Technical Specifications, Manuals and Documentation

Artisan Scientific is Your Source for Quality New and Certified-Used/Pre-owned Equipment

- Tens of Thousands of In-Stock Items
- Hundreds of Manufacturers Supported
- Fast Shipping and Delivery
- Leasing / Monthly Rentals
- Equipment Demos
- Consignment

Service Center Repairs

Experienced Engineers and Technicians on staff in our State-of-the-art Full-Service In-House Service Center Facility

InstraView™ Remote Inspection

Remotely inspect equipment before purchasing with our Innovative InstraView™ website at <http://www.instraview.com>

We buy used equipment! We also offer credit for Buy-Backs and Trade-Ins

Sell your excess, underutilized, and idle used equipment. Contact one of our Customer Service Representatives today!

Talk to a live person: 888-88-SOURCE (888-887-6872) | Contact us by email: sales@artisan-scientific.com | Visit our website: <http://www.artisan-scientific.com>